

# First Impressions

DENTAL LAB LLC

Quality, Esthetics, & Service Since 1992

700 N. Neely St. #17 Phone (480) 545-1460  
Gilbert, AZ 85233-3826

Email: office@firstimpressions-dentallab.com  
Website www.firstimpressions-dentallab.com

## REMOVABLE RESTORATION Rx\*

Pan # \_\_\_\_\_

Office / Dr. \_\_\_\_\_

Patient Name \_\_\_\_\_

Date Sent \_\_\_\_\_ Due Date \_\_\_\_\_

SIGNATURE \_\_\_\_\_

LICENSE NO. \_\_\_\_\_

RX MUST BE SIGNED WITH LICENSE NUMBER TO BE VALID.

### TYPE OF RESTORATION

- |   |   |   |
|---|---|---|
| <input type="checkbox"/> Metal Framework      | <input type="checkbox"/> Reline               | <input type="checkbox"/> Custom Tray                |
| <input type="checkbox"/> Acrylic Denture      | <input type="checkbox"/> Hard                 | <input type="checkbox"/> Perforated                 |
| <input type="checkbox"/> Complete             | <input type="checkbox"/> Soft                 | <input type="checkbox"/> Non-Perforated             |
| <input type="checkbox"/> Partial              | <input type="checkbox"/> Rebase               |   |
| <input type="checkbox"/> Immediate            | <input type="checkbox"/> Add Clasp on # _____ | <input type="checkbox"/> Night Guard                |
| <input type="checkbox"/> Add Tooth on # _____ |   | <input type="checkbox"/> Soft Vacuum                |
|   |   | <input type="checkbox"/> Hard Thermoforming         |
|   |   | <input type="checkbox"/> Hard/Soft Thermoforming    |
|   |   | <input type="checkbox"/> Clearsplint Self Adjusting |

### ARCH

- Upper  Lower
- Upper and Lower

### METAL

- CoCr
- Cast Frame / Valplast Combo

### ACRYLIC

- Conventional
- Lucitone 199
- Valplast
- Injection (IVOCAP)

### SERVICE DESIRED

- Direct Finish
- Metal Framework Try-In
- Metal Frame + Bite Block(s)
- Metal Frame + Teeth Set Up
- Teeth Set Up Only
- Teeth Set Up + Acrylic Processing
- Acrylic Denture Try-In
- Base Plate + Bite Rim / Block
- Base Plate + Teeth Set Up
- Acrylic Processing Only

### TEETH

- Anteriors
- Ivoclar
- Classic
- House Brand
- Posteriors
- 0°
- 10°
- 20°
- 30°
- 33°

### FESTOONING

- Smooth  Light  Medium


SHADE \_\_\_\_\_

MOULD \_\_\_\_\_

### FRAMEWORK DESIGN REST

- Lab to Design  Mesial Rest on # \_\_\_\_\_
- See Drawing on Rx  Distal Rest on # \_\_\_\_\_
- See Drawing on Cast  Cingulum Rest on # \_\_\_\_\_

### DESIGN



### SPECIAL INSTRUCTIONS